

SALLI SWINGFIT



On Salli SwingFit you can train your core muscles during the work day!

The swing mechanism of Salli SwingFit enables the seat to move in all directions, without a separate adjustment lever. Thus you can exercise while sitting, which adds to the mobility and metabolism of the lower back, and activates the whole body.

SEAT


- Two-part active seat with width adjustment
- 3 mm steel sheet seat plate
- Leather, artificial leather, ESD artificial leather, or wool

GAS SPRINGS


	User height (cm)	Chair height Regular gas spring (mm, min-max)	Chair height Gas spring with Top&Bottom (mm, min-max)
Short	under 155	510-640	520-650
Medium	155-180	590-785	640-830
Long	over 170	665-925	680-940

Mini gas spring is available for special circumstances; use depends on the working height, not on the height of the user.

Note! If you are using industrial or inline castors, the chair is 35 mm higher than the measurements shown in the table.



Swing-mechanism



Width adjustment



TECHNICAL FEATURES

- Total weight 11.7 kg
- Height control by hand as a standard; Top & Bottom (foot height control) available
- Maximum load 120 kg
- Warranty 10 years

BASES



Salli Base

- Ø 560 mm, aluminium
- Metallic or black



Aluminium base

- Ø 540 mm
- Metallic or black



Plastic base

- Ø 580 mm
- Black

CASTORS



Soft standard

- Ø 65 mm
- For hard floors



Inline Industrial

- Ø 75 mm
- For uneven floors, ideal also for hairdressers and on wall-to-wall carpets

LEATHER



ARTIFICIAL LEATHER



WOOL



ESD ARTIFICIAL LEATHER



SEAT COVERS



ACCESSORIES

Suitable For **Salli SwingFit**

ALLROUND

Allround moves freely on all sides of the chair, and also around its own axis. Can be used as a support for either one arm or both arms.



TOB & BOTTOM

Enables height adjustment without using the lever by hand. Recommended for hygienic environments, such as operating theatres and dental clinics.



FOOT SUPPORT

A perfect accessory for high workstations to support the feet. Recommended for temporary use only. Ø 460 mm.

